

Kellems Wire Management, Cord Connectors, Straight Male, .19-.25", 1/4", Nylon

By Hubbell Wiring Device-Kellems
Catalog # [SHC1003CR](#)



Kellems Wire Management, Cord Connectors, Straight Male, .19-.25", 1/4", Nylon

Application

Straight Male- Form 1

Performance

- Environmental - Flammability - UL 94-V2
- Environmental - Hazardous Locations - Used in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 in accordance with the NEC
- Environmental - Operating Temperatures - -30°F to +225°F (-34°C to +107°C)

General

Catalog Number	SHC1003CR
Color	Gray
Color Code	Red
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Nylon Washer Between Box And Fitting.
Item Type	Cord Connectors
Material	Nylon
Material - Mounting Hardware Series	Locknut or Tapped Opening Standard Duty
Specifications	<ul style="list-style-type: none">• Cord Diameter Range Inches (mm) - .19"- .25" (4.7-6.3)• Form Size - F1• Material - Gray Nylon

Temperature Rating	• NPT Hub Size - 1/4 Inch Minimum -30 Deg F to 225 Deg F (-34 Deg C to 107 Deg C)
Type UPC	Straight Male 783585207858

Dimensions

Display Size	1/4" NPT
Hub Size	1/4"

Conductor Related

Conductor Range	0.19-0.25 in (4.7- 6.3 mm)
Number of Conductors	Single

Certifications And Compliance

Industry Standard(s)	UL Listed
Nema Rating	NEMA Type 4, 4X, 12 and 13
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	25
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Literature - Wire Management Solutions Brochure](#)
[Specifications - SHC1003CR](#)
[Warranty - Industrial & Commercial Products](#)