

Kellems Wire Management, Cord Connectors, Straight Male, .13-.19", 3/8", Aluminum

By Hubbell Wiring Device-Kellems
Catalog # SHC1008



Kellems Wire Management, Cord Connectors, Straight Male,
.13-.19", 3/8", Aluminum

Application

- Straight Male- Form 1

Performance

- Environmental - Hazardous Locations - Used in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 in accordance with the NEC
- Environmental - Operating Temperatures - -30°F to +225°F (-34°C to +107°C)

General

Catalog Number	SHC1008
Color Code	Orange
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Nylon Washer Between Box And Fitting.
Item Type	Cord Connectors
Material	Aluminum
Material - Mounting Hardware Series	Locknut or Tapped Opening Standard Duty
Specifications	<ul style="list-style-type: none">• Cord Diameter Range Inches (mm) - .13"- .19" (3.2-4.7)• Form Size - F1• Material - Aluminum• NPT Hub Size - 3/8 Inch

Temperature Rating

Minimum -30 Deg F to 225 Deg F (-34 Deg C to 107 Deg C)

Type
UPC

Straight Male
783585200088

Dimensions

Display Size
Hub Size

3/8" NPT
3/8"

Conductor Related

Conductor Range
Number of Conductors

0.13-0.19 in (3.2- 4.7 mm)
Single

Certifications And Compliance

Industry Standard(s)
Nema Rating
Standards - RoHS Compliance Status

UL Listed
NEMA Type 4, 4X, 12 and 13
CM

Logistics

Carton Quantity

50

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Literature - Wire Management Solutions Brochure](#)
[Specifications - SHC1008](#)
[Warranty - Industrial & Commercial Products](#)