

Kellems Wire Management, Cord Connectors, Straight Male, .19-.25", 3/8", Aluminum

By Hubbell Wiring Device-Kellems
Catalog # [SHC1009](#)

Kellems Wire Management, Cord Connectors, Straight Male, .19-.25", 3/8", Aluminum

Application

- Straight Male- Form 1

Performance

- Environmental - Hazardous Locations - Used in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 in accordance with the NEC
- Environmental - Operating Temperatures - -30°F to +225°F (-34°C to +107°C)

General

Catalog Number	SHC1009
Color Code	Red
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Nylon Washer Between Box And Fitting.
Item Type	Cord Connectors
Material	Aluminum
Material - Mounting Hardware	Locknut or Tapped Opening
Series	Standard Duty
Specifications	<ul style="list-style-type: none">• Cord Diameter Range Inches (mm) - .19"- .25" (4.7-6.3)• Form Size - F1• Material - Aluminum• NPT Hub Size - 3/8 Inch



Temperature Rating	Minimum -30 Deg F to 225 Deg F (-34 Deg C to 107 Deg C)
Type	Straight Male
UPC	783585200095

Dimensions

Display Size	3/8" NPT
Hub Size	3/8"

Conductor Related

Conductor Range	0.19-0.25 in (4.7- 6.3 mm)
Number of Conductors	Single

Certifications And Compliance

Industry Standard(s)	UL Listed
Nema Rating	NEMA Type 4, 4X, 12 and 13
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	50
Pallet Quantity	22000

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Literature - Wire Management Solutions Brochure](#)
[Specifications - SHC1009](#)
[Warranty - Industrial & Commercial Products](#)