

## Kellems Wire Management, Cord Connectors, Straight Male, .38-.44", 3/8", Aluminum

By Hubbell Wiring Device-Kellems  
Catalog # [SHC1012](#)



Kellems Wire Management, Cord Connectors, Straight Male, .38-.44", 3/8", Aluminum

### Application

- Straight Male- Form 1

### Performance

- Environmental - Hazardous Locations - Used in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 in accordance with the NEC
- Environmental - Operating Temperatures - -30°F to +225°F (-34°C to +107°C)

### General

Catalog Number	SHC1012
Color	Metallic
Color Code	Blue
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Nylon Washer Between Box And Fitting.
Item Type	Cord Connectors
Material	Machined Aluminum
Material - Mounting Hardware	Locknut or Tapped Opening
Series	Standard Duty
Specifications	<ul style="list-style-type: none"><li>• Cord Diameter Range Inches (mm) - .38"- .44" (9.5-11.0)</li><li>• Form Size - F1</li><li>• Material - Aluminum</li><li>• NPT Hub Size - 3/8 Inch</li></ul>

Temperature Rating

Minimum -30 Deg F to 225 Deg F (-34 Deg C to 107 Deg C)

Type  
UPC

Straight Male  
783585200125

### Dimensions

Display Size 3/8" NPT  
Hub Size 3/8"

### Conductor Related

Conductor Range 0.38- 0.44 in (9.5-11.0 mm)  
Number of Conductors Single

### Certifications And Compliance

Industry Standard(s) UL Listed  
Nema Rating NEMA Type 4, 4X, 12 and 13  
Standards - RoHS Compliance CM  
Status

### Logistics

Carton Quantity 50  
Pallet Quantity 22000

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Literature - Wire Management Solutions Brochure](#)  
[Specifications - SHC1012](#)  
[Warranty - Industrial & Commercial Products](#)