

Kellems Wire Management, Cord Connectors, Straight Male, .38-.44", 3/8", Nylon

By Hubbell Wiring Device-Kellems

Catalog # [SHC1012CR](#)

Kellems Wire Management, Cord Connectors, Straight Male, .38-.44", 3/8", Nylon



General

Application	Straight Male- Form 1
Catalog Number	SHC1012CR
Color	Gray
Color Code	Blue
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Nylon Washer Between Box And Fitting.
Item Type	Cord Connectors
Material	Nylon
Material - Mounting Hardware	Locknut or Tapped Opening
Performance	Environmental - Flammability - UL 94-V2 Environmental - Hazardous Locations - Used in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 in accordance with the NEC Environmental - Operating Temperatures - -30°F to +225°F (-34°C to +107°C)
Series	Standard Duty
Temperature Rating	Minimum -30 Deg F to 225 Deg F (-34 Deg C to 107 Deg C)
Type	Straight Male
UPC	783585207940

Dimensions

Display Size	3/8" NPT
Hub Size	3/8"

Conductor Related

Conductor Range	0.38- 0.44 in (9.5-11.0 mm)
Number of Conductors	Single

Certifications And Compliance

Industry Standard(s)	UL Listed
Nema Rating	NEMA Type 4, 4X, 12 and 13

Logistics

Carton Quantity	50
-----------------	----

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-SHC1012CR-SPEC-EN | REV 6/2024