

# Kellems Wire Management, Cord Connectors, Straight Male, .19-.25", 1/2", Steel

By Hubbell Wiring Device-Kellems  
Catalog # [SHC1021ZP](#)



Kellems® Straight Male Cord Connector, .19-.25", 1/2", Steel

## Application

- Straight Male- Form 2

## Performance

- Environmental - Hazardous Locations - Used in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 in accordance with the NEC
- Environmental - Operating Temperatures - -30°F to +225°F (-34°C to +107°C)

## General

Catalog Number	SHC1021ZP
Color Code	Red
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Nylon Washer Between Box And Fitting.
Item Type	Cord Connectors
Material	Steel, Zinc Plated
Material - Mounting Hardware	Locknut or Tapped Opening
Series	Standard Duty
Specifications	<ul style="list-style-type: none"><li>• Cord Diameter Range Inches (mm) - .19"-.25" (4.7-6.3)</li><li>• Form Size - F2</li><li>• Material - Zinc-Plated Steel</li><li>• NPT Hub Size - 1/2 Inch</li></ul>

Temperature Rating

Minimum -30 Deg F to 225 Deg F (-34 Deg C to 107 Deg C)

Type  
UPC

Straight Male  
783585210216

## Dimensions

Display Size 1/2" NPT  
Hub Size 1/2 "

## Conductor Related

Conductor Range 0.19-0.25 in (4.7- 6.3 mm)  
Number of Conductors Single

## Certifications And Compliance

Industry Standard(s) UL Listed  
Nema Rating NEMA Type 4, 4X, 12 and 13

## Logistics

Carton Quantity 25  
Pallet Quantity 10400

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Literature - Wire Management Solutions Brochure](#)  
[Specifications - SHC1021ZP](#)  
[Warranty - Industrial & Commercial Products](#)