

Kellems Wire Management, Cord Connectors, Straight Male, .25-.38", 1/2", Aluminum

By Hubbell Wiring Device-Kellems
Catalog # [SHC1022](#)



Kellems Wire Management, Cord Connectors, Straight Male, .25-.38", 1/2", Aluminum

Application

- Straight Male- Form 2

Performance

- Environmental - Hazardous Locations - Used in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 in accordance with the NEC
- Environmental - Operating Temperatures - -30°F to +225°F (-34°C to +107°C)

General

Catalog Number	SHC1022
Color Code	White
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Nylon Washer Between Box And Fitting.
Item Type	Cord Connectors
Material	Aluminum
Material - Mounting Hardware Series	Locknut or Tapped Opening Standard Duty
Specifications	<ul style="list-style-type: none">• Cord Diameter Range Inches (mm) - .25"-.38" (6.3-.9.7)• Form Size - F2• Material - Aluminum• NPT Hub Size - 1/2 Inch
Temperature Rating	Minimum -30 Deg F to 225 Deg F (-34 Deg C to 107 Deg C)

Type	Straight Male
UPC	783585200224

Dimensions

Display Size	1/2" NPT
Hub Size	1/2 "

Conductor Related

Conductor Range	0.25- 0.38 in (6.3- .9.7 mm)
Number of Conductors	Single

Certifications And Compliance

Industry Standard(s)	UL Listed
Nema Rating	NEMA Type 4, 4X, 12 and 13
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	50
Pallet Quantity	16000

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Literature - Multi-Hole Cord Grip Connectors](#)
- [Specifications - SHC1022](#)
- [Warranty - Industrial & Commercial Products](#)