

Kellems Wire Management, Cord Connectors, Straight Male, .25-.38", 1/2", Steel

By Hubbell Wiring Device-Kellems

Catalog # [SHC1022ZP](#)



Kellems® Straight Male Cord Connector, .25-.38", 1/2", Steel

General

Application	Straight Male- Form 2
Catalog Number	SHC1022ZP
Color	
Color Code	White
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Nylon Washer Between Box And Fitting.
Item Type	Cord Connectors
Material	Steel, Zinc Plated
Material - Mounting Hardware	Locknut or Tapped Opening
Performance	Environmental - Hazardous Locations - Used in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 in accordance with the NEC Environmental - Operating Temperatures - -30°F to +225°F (-34°C to +107°C)
Series	Standard Duty
Temperature Rating	Minimum -30 Deg F to 225 Deg F (-34 Deg C to 107 Deg C)
Type	Straight Male Straight Male
UPC	783585210223

Dimensions

Display Size	1/2" NPT
Hub Size	1/2 "

Conductor Related

Conductor Range	0.25- 0.38 in (6.3- 9.7 mm)
Number of Conductors	Single

Certifications And Compliance

Industry Standard(s)	UL Listed
Nema Rating	NEMA Type 4, 4X, 12 and 13
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	25
Pallet Quantity	11400

Product Assets

[Catalogs - WDK Catalog Full 2024](#)

[Literature - Wire Management Solutions Brochure](#)

[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-SHC1022ZP-SPEC-EN | REV 6/2024