

Kellems Wire Management, Cord Connectors, Straight Male, .38-.50", 1/2", Nylon

By Hubbell Wiring Device-Kellems
Catalog # SHC1023CR



Kellems Wire Management, Cord Connectors, Straight Male, .38-.50", 1/2", Nylon

Application

- Straight Male- Form 2

Performance

- Environmental - Flammability - UL 94-V2
- Environmental - Hazardous Locations - Used in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 in accordance with the NEC
- Environmental - Operating Temperatures - -30°F to +225°F (-34°C to +107°C)

General

Catalog Number	SHC1023CR
Color	Gray
Color Code	Blue
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Nylon Washer Between Box And Fitting.
Item Type	Cord Connectors
Material	Nylon
Material - Mounting Hardware Series	Locknut or Tapped Opening Standard Duty
Specifications	<ul style="list-style-type: none">• Cord Diameter Range Inches (mm) - .38"- .50" (9.7-12.7)• Form Size - F2• Material - Gray Nylon• NPT Hub Size - 1/2 Inch

Temperature Rating

Minimum -30 Deg F to 225 Deg F (-34 Deg C to 107 Deg C)

Type
UPC

Straight Male
783585208053

Dimensions

Display Size 1/2" NPT
Hub Size 1/2"

Conductor Related

Conductor Range 0.38- 0.5 in (9.7- 12.7 mm)
Number of Conductors Single

Certifications And Compliance

Industry Standard(s) UL Listed
Nema Rating NEMA Type 4, 4X, 12 and 13
Standards - RoHS Compliance CM
Status

Logistics

Carton Quantity 25
Pallet Quantity 12600

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Literature - Wire Management Solutions Brochure](#)
[Literature - Multi-Hole Cord Grip Connectors](#)
[Specifications - SHC1023CR](#)
[Warranty - Industrial & Commercial Products](#)