

## Kellems Wire Management, Cord Connectors, Straight Male, .63-.75", 1/2", Aluminum

By Hubbell Wiring Device-Kellems  
Catalog # [SHC1027](#)

Kellems Wire Management, Cord Connectors, Straight Male, .63-.75", 1/2", Aluminum

### Application

- Straight Male- Form 3

### Performance

- Environmental - Hazardous Locations - Used in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 in accordance with the NEC
- Environmental - Operating Temperatures - -30°F to +225°F (-34°C to +107°C)

### General

Catalog Number	SHC1027
Color Code	Yellow
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Nylon Washer Between Box And Fitting.
Item Type	Cord Connectors
Material	Aluminum
Material - Mounting Hardware Series	Locknut or Tapped Opening Standard Duty
Specifications	<ul style="list-style-type: none"><li>• Cord Diameter Range Inches (mm) - .63"-.75" (15.9-19.0)</li><li>• Form Size - F3</li><li>• Material - Aluminum</li><li>• NPT Hub Size - 1/2 Inch</li></ul>



Temperature Rating	Minimum -30 Deg F to 225 Deg F (-34 Deg C to 107 Deg C)
Type	Straight Male
UPC	783585200279

### Dimensions

Display Size	1/2" NPT
Hub Size	1/2 "

### Conductor Related

Conductor Range	0.63- 0.75 in (15.9- 19.0 mm)
Number of Conductors	Single

### Certifications And Compliance

Industry Standard(s)	UL Listed
Nema Rating	NEMA Type 4, 4X, 12 and 13
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	30
Pallet Quantity	9450

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Literature - Wire Management Solutions Brochure](#)  
[Specifications - SHC1027](#)  
[Warranty - Industrial & Commercial Products](#)