

Kellems Wire Management, Cord Connectors, Straight Male, .25-.38", 3/4", Steel

By Hubbell Wiring Device-Kellems
Catalog # [SHC1032ZP](#)



Kellems® Straight Male Cord Connector, .25-.38", 3/4", Steel

Application

- Straight Male- Form 2

Performance

- Environmental - Hazardous Locations - Used in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 in accordance with the NEC
- Environmental - Operating Temperatures - -30°F to +225°F (-34°C to +107°C)

General

Catalog Number	SHC1032ZP
Color Code	White
EU RoHS Indicator	No
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Nylon Washer Between Box And Fitting.
Item Type	Cord Connectors
Material	Steel, Zinc Plated
Material - Mounting Hardware	Locknut or Tapped Opening
Series	Standard Duty
Specifications	<ul style="list-style-type: none">• Cord Diameter Range Inches (mm) - .25"- .38" (6.3-9.7)• Form Size - F2• Material - Zinc-Plated Steel

Temperature Rating	• NPT Hub Size - 3/4 Inch Minimum -30 Deg F to 225 Deg F (-34 Deg C to 107 Deg C)
Type	Straight Male
UPC	783585496139

Dimensions

Display Size	3/4" NPT
Hub Size	3/4"

Conductor Related

Conductor Range	0.25- 0.38 in (6.3- 9.7 mm)
Number of Conductors	Single

Certifications And Compliance

Industry Standard(s)	UL Listed
Nema Rating	NEMA Type 4, 4X, 12 and 13

Logistics

Carton Quantity	25
-----------------	----

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Specifications - SHC1032ZP](#)
- [Warranty - Industrial & Commercial Products](#)