

Kellems Wire Management, Cord Connectors, Straight Male, .38-.50", 3/4", Steel

By Hubbell Wiring Device-Kellems
Catalog # [SHC1033ZP](#)



Kellems® Straight Male Cord Connector, .38-.50", 3/4", Steel

Application

- Straight Male- Form 2

Performance

- Environmental - Hazardous Locations - Used in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 in accordance with the NEC
- Environmental - Operating Temperatures - -30°F to +225°F (-34°C to +107°C)

General

| | |
|-------------------------------------|---|
| Catalog Number | SHC1033ZP |
| Color Code | Blue |
| EU RoHS Indicator | Yes |
| Environmental Conditions | Suitable For Use In Wet Locations When Used With A Listed Nylon Washer Between Box And Fitting. |
| Item Type | Cord Connectors |
| Material | Steel, Zinc Plated |
| Material - Mounting Hardware Series | Locknut or Tapped Opening Standard Duty |
| Specifications | <ul style="list-style-type: none">• Cord Diameter Range Inches (mm) - .38"- .50" (9.7-12.7)• Form Size - F2• Material - Zinc-Plated Steel• NPT Hub Size - 3/4 Inch |

Temperature Rating

Minimum -30 Deg F to 225 Deg F (-34 Deg C to 107 Deg C)

Type
UPC

Straight Male
783585496177

Dimensions

Display Size
Hub Size

3/4" NPT
3/4"

Conductor Related

Conductor Range
Number of Conductors

0.38- 0.5 in (9.7- 12.7 mm)
Single

Certifications And Compliance

Industry Standard(s)
Nema Rating

UL Listed
NEMA Type 4, 4X, 12 and 13

Logistics

Carton Quantity
Pallet Quantity

25
9600

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Literature - Wire Management Solutions Brochure](#)
[Specifications - SHC1033ZP](#)
[Warranty - Industrial & Commercial Products](#)