

## Kellems Wire Management, Cord Connectors, Straight Male, .38"-.50", 3/4", Aluminum

By Hubbell Wiring Device-Kellems  
Catalog # SHC1035CR



Kellems Wire Management, Cord Connectors, Straight Male, .38"-.50", 3/4", Aluminum

### Application

Straight Male- Form 3

### Performance

- Environmental - Flammability - UL 94-V2
- Environmental - Hazardous Locations - Used in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 in accordance with the NEC
- Environmental - Operating Temperatures - -30°F to +225°F (-34°C to +107°C)

### General

Catalog Number	SHC1035CR
Color	Gray
Color Code	Blue
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Nylon Washer Between Box And Fitting.
Item Type	Cord Connectors
Material	Nylon
Material - Mounting Hardware Series	Locknut or Tapped Opening Standard Duty
Specifications	<ul style="list-style-type: none"><li>• Cord Diameter Range Inches (mm) - .38"-.50" (9.5-12.7)</li><li>• Form Size - F3</li><li>• Material - Gray Nylon</li><li>• NPT Hub Size - 3/4 Inch</li></ul>
Temperature Rating	Minimum -30 Deg F to 225 Deg F (-34 Deg C to 107 Deg C)
Type	Straight Male
UPC	783585208077

### Dimensions

Dimensions	2.15 in x 1.56 in x 1.56 in
Display Size	3/4" NPT
Height	1.56 in
Hub Size	3/4"
Length	2.15 in
Weight	0.1 lb
Width	1.56 in

### Conductor Related

Conductor Range	0.38- 0.5 in (9.5- 12.7 mm)
Number of Conductors	Single

### Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>• UL Listed In Accordance With Standard 514B For Indoor/Outdoor Use</li><li>• United States Coast Guard Approved, Title 46-Part 111</li></ul>
Nema Rating	NEMA Type 4, 4X, 12 and 13
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	25
Pallet Quantity	7875

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Literature - Wire Management Solutions Brochure](#)  
[Specifications - SHC1035CR](#)  
[Warranty - Industrial & Commercial Products](#)