

Kellems Wire Management, Cord Connectors, Straight Male, .63-.75", 3/4", Aluminum

By Hubbell Wiring Device-Kellems
Catalog # [SHC1037](#)



Kellems Wire Management, Cord Connectors, Straight Male, .63-.75", 3/4", Aluminum

Application

- Straight Male- Form 3

Performance

- Environmental - Hazardous Locations - Used in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 in accordance with the NEC
- Environmental - Operating Temperatures - -30°F to +225°F (-34°C to +107°C)

General

Catalog Number	SHC1037
Color Code	Yellow
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Nylon Washer Between Box And Fitting.
Item Type	Cord Connectors
Material	Aluminum
Material - Mounting Hardware	Locknut or Tapped Opening
Series	Standard Duty
Specifications	<ul style="list-style-type: none">• Cord Diameter Range Inches (mm) - .63"- .75" (15.9-19.0)• Form Size - F3• Material - Aluminum• NPT Hub Size - 3/4 Inch

Temperature Rating

Minimum -30 Deg F to 225 Deg F (-34 Deg C to 107 Deg C)

Type
UPC

Straight Male
783585200378

Dimensions

Display Size
Hub Size

3/4" NPT
3/4"

Conductor Related

Conductor Range
Number of Conductors

0.63- 0.75 in (15.9- 19.0 mm)
Single

Certifications And Compliance

Industry Standard(s)
Nema Rating
Standards - RoHS Compliance
Status

UL Listed
NEMA Type 4, 4X, 12 and 13
CM

Logistics

Carton Quantity
Pallet Quantity

30
9600

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Literature - Wire Management Solutions Brochure](#)
[Specifications - SHC1037](#)
[Warranty - Industrial & Commercial Products](#)