

Kellems Wire Management, Cord Connectors, Straight Male, .75-.88", 3/4", Aluminum

By Hubbell Wiring Device-Kellems
Catalog # [SHC1038](#)



Kellems Wire Management, Cord Connectors, Straight Male, .75-.88", 3/4", Aluminum

Application

- Straight Male- Form 3

Performance

- Environmental - Hazardous Locations - Used in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 in accordance with the NEC
- Environmental - Operating Temperatures - -30°F to +225°F (-34°C to +107°C)

General

Catalog Number	SHC1038
Color Code	Orchid
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Nylon Washer Between Box And Fitting.
Item Type	Cord Connectors
Material	Aluminum
Material - Mounting Hardware	Locknut or Tapped Opening
Series	Standard Duty
Specifications	<ul style="list-style-type: none">• Cord Diameter Range Inches (mm) - .75"- .88" (19.0-22.2)• Form Size - F3• Material - Aluminum• NPT Hub Size - 3/4 Inch

Temperature Rating

Minimum -30 Deg F to 225 Deg F (-34 Deg C to 107 Deg C)

Type
UPC

Straight Male
783585200385

Dimensions

Display Size 3/4" NPT
Hub Size 3/4"

Conductor Related

Conductor Range 0.75- 0.88 in (19.0- 22.2 mm)
Number of Conductors Single

Certifications And Compliance

Industry Standard(s) UL Listed
Nema Rating NEMA Type 4, 4X, 12 and 13
Standards - RoHS Compliance CM
Status

Logistics

Carton Quantity 30
Pallet Quantity 9450

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Literature - Wire Management Solutions Brochure](#)
[Specifications - SHC1038](#)
[Warranty - Industrial & Commercial Products](#)