

# Kellems Wire Management, Cord Connectors, Straight Male, .88-1.00", 1", Aluminum

By Hubbell Wiring Device-Kellems  
Catalog # [SHC1043](#)



Kellems Wire Management, Cord Connectors, Straight Male, .88-1.00", 1", Aluminum

## Application

- Straight Male- Form 4

## Performance

- Environmental - Hazardous Locations - Used in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 in accordance with the NEC
- Environmental - Operating Temperatures - -30°F to +225°F (-34°C to +107°C)

## General

Catalog Number	SHC1043
Color Code	Gray
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Nylon Washer Between Box And Fitting.
Item Type	Cord Connectors
Material	Aluminum
Material - Mounting Hardware Series	Locknut or Tapped Opening Standard Duty
Specifications	<ul style="list-style-type: none"><li>• Cord Diameter Range Inches (mm) - .88"-1.00" (22.2-25.4)</li><li>• Form Size - F4</li><li>• Material - Aluminum</li><li>• NPT Hub Size - 1 Inch</li></ul>

Temperature Rating

Minimum -30 Deg F to 225 Deg F (-34 Deg C to 107 Deg C)

Type  
UPC

Straight Male  
783585200439

## Dimensions

Display Size 1" NPT  
Hub Size 1"

## Conductor Related

Conductor Range 0.88-1 in (22.2- 25.4 mm)  
Number of Conductors Single

## Certifications And Compliance

Industry Standard(s) UL Listed  
Nema Rating NEMA Type 4, 4X, 12 and 13  
Standards - RoHS Compliance CM  
Status

## Logistics

Carton Quantity 15  
Pallet Quantity 4725

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Literature - Wire Management Solutions Brochure](#)  
[Specifications - SHC1043](#)  
[Warranty - Industrial & Commercial Products](#)