

## Straight Blade Devices, Receptacles, Duplex, SNAPConnect, Hospital Grade, 20A 125V, 2-Pole 3- Wire Grounding, 5-20R, Nylon, Ivory

By Hubbell Wiring Device-Kellems  
Catalog # [SNAP8300IA](#)

Straight Blade Devices, Receptacles, Duplex, SNAPConnect,  
Hospital Grade, 20A 125V, 2-Pole 3-Wire Grounding, 5-20R,  
Nylon, Ivory



### Performance

- Electrical: Current Interrupting- Certified for current interrupting at full rated current
- Electrical: Dielectric Voltage- Withstands 2,000V minimum
- Mechanical: Product Identification Ratings are a permanent part of the device
- Environmental: Flammability- UL 94V-2
- Environmental: Operating Temperature- Maximum continuous 75°C
- minimum -40°C (w/o impact)

### General

Catalog Number	SNAP8300IA
Color	Ivory
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Horsepower - Maximum	1
Item Type	Finder Groove Face
Material	Nylon
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	Hospital Grade
Specifications	<ul style="list-style-type: none"> <li>• Automatic Self-grounding Clip - Stainless steel</li> <li>• Base - PBT</li> <li>• Face - Nylon</li> <li>• Ground Contacts - Brass</li> <li>• Mounting Screws - Zinc plated steel</li> <li>• Mounting Strap - Brass</li> <li>• Power Contacts - Brass</li> </ul>
Style	Finder Groove Face
Type	Standard Duplex
UPC	783585247656

### Dimensions

Dimensions	3.28 in x 1.64 in x 1.1 in
Display Size	Standard Sized Product
Height	1.1 in
Length	3.28 in
Weight	0.2 lb
Width	1.64 in

### Electrical Ratings

Amperage Rating	20 A
Connectivity	Connectorized
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Phase	Single Phase
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500 W

### Conductor Related

Number Of Wires	3-Wire
Number of Conductors	3-Wire Grounding
Wire Size	#12 AWG

### Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"> <li>• CSA Certified, C22.2, No. 42 File 285</li> <li>• Fed. Spec. W-C-596</li> <li>• NEMA® WD-6 Compliant</li> <li>• UL Listed to UL498 File No. E2186</li> </ul>
Nema Rating	5-20R
Standards - RoHS Compliance	CM
Status	

### Logistics

Carton Quantity	10
-----------------	----

Pallet Quantity

4500

Catalogs - WDK Catalog Full 2024

Literature - Electrical Products - Healthcare Solutions

Specifications - SNAP8300IA

Warranty - Industrial & Commercial Products

**Product Assets**



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-SNAP8300IA-SPEC-EN | REV 10/2024