


Wallplates and Boxes, Metallic Plates, 2- Gang, 2) Toggle Openings, Standard Size, Stainless Steel

By Hubbell Wiring Device-Kellems
Catalog # [SS2](#)



Wallplates and Boxes, Metallic Plates, 2- Gang, 2) Toggle
Openings, Standard Size, Stainless Steel

General

Catalog Number	SS2
Construction	Stamped
Cutout	2) Toggle
EU RoHS Indicator	Yes
Item Type	Toggle Switch Plate
Material	Stainless Steel, Type 302/304
Material - Mounting Hardware	Screw Mounting
Number of Gang(s)	2-Gang
Operating Temperature	-40°C to 85 °C
Orientation	Vertical Mount
Size	Standard
Specifications	<ul style="list-style-type: none">• Appearance - Horizontal brushed finish• Mounting Screws - 302/304 SS, Slotted Head• Plate Material - Stainless steel 302/304• Plate Openings - Toggle switch• Plate Type - 2-Gang 2-Toggle
Style	2-Toggle

Type	Toggle
UPC	883778200809

Dimensions

Display Size	Standard Sized
Thickness	0.035

Certifications And Compliance

Industry Standard(s)	UL Listed
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
Pallet Quantity	8000

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Specifications - SS2](#)
[Warranty - Industrial & Commercial Products](#)