

# Straight Blade Devices, Explosion Proof, Male Plug, 20A 125V, 5-20P, Single Pack

By Hubbell Wiring Device-Kellems  
Catalog # [UGP20231](#)



Straight Blade Devices, Explosion Proof, Male Plug, 20A 125V, 5-20P, Single Pack

## Features

- Explosion Proof
- Male Plug
- 20A 125V
- 5-20P

## Performance

- Electrical - Current Interrupting - Certified for current interrupting at full rated current
- Electrical - Dielectric Voltage - Withstands 2,000V minimum
- Environmental - Flammability - UL 94 HB or better
- Environmental - Operating Temperatures - Maximum continuous 75°C minimum -40°C (w/o impact)
- Mechanical - Product Identification - Ratings are a permanent part of the device
- Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA

## General

Catalog Number	UGP20231
Color	Metallic
EU RoHS Indicator	Contact Manufacturer
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
UPC	783585412405

## Dimensions

Dimensions	2.55 in x 1.69 in x 1.69 in
------------	-----------------------------

Height	1.69 in
Length	2.55 in
Weight	0.4 lb
Width	1.69 in

## Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	125 V
Voltage Rating Description	125 V
Wattage	2500 W

## Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

## Certifications And Compliance

Industry Standard(s)	Listed to UL Standard 498
Nema Rating	5-20P

## Logistics

Carton Quantity	10
Pallet Quantity	1600

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - UGP20231](#)  
[Warranty - Industrial & Commercial Products](#)