

Kellems Wire Management, Cord Connectors, 45 Degree Male, .25-.38", 1/2", Aluminum

By Hubbell Wiring Device-Kellems
Catalog # [VHC1022](#)



Kellems Wire Management, Cord Connectors, 45 Degree Male, .25-.38", 1/2", Aluminum

Application

45 Degree Male- Form 2

Performance

- Environmental - Hazardous Locations - Used in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 in accordance with the NEC.
- Environmental - Operating Temperatures - -30°F to +225°F (-34°C to +107°C)

General

Catalog Number	VHC1022
Color Code	White
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Nylon Washer Between Box And Fitting.
Item Type	Cord Connectors
Material	Aluminum
Material - Mounting Hardware	Locknut or Tapped Opening
Series	Standard Duty
Specifications	<ul style="list-style-type: none">• Cord Diameter Inches (mm) - .25"-.38"(6.3-9.7)• Form Size - F2• Material - Aluminum

Temperature Rating

- NPT Hub Size - 1/2 Inch
Minimum -30 Deg F to 225 Deg F (-34 Deg C to 107 Deg C)

Type
UPC

45 Degree Male
783585202228

Dimensions

Display Size
Hub Size

1/2" NPT
1/2 "

Conductor Related

Conductor Range
Number of Conductors

0.25- 0.38 in (6.3- 9.7 mm)
Single

Certifications And Compliance

Industry Standard(s)
Nema Rating

UL Listed
NEMA Type 4, 4X, 12 and 13

Logistics

Carton Quantity

25

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Literature - Wire Management Solutions Brochure](#)
[Specifications - VHC1022](#)
[Warranty - Industrial & Commercial Products](#)