

# Kellems Wire Management, Cord Connectors, 45 Degree Male, .63-.75", 3/4", Aluminum

By Hubbell Wiring Device-Kellems  
Catalog # [VHC1037](#)



Kellems Wire Management, Cord Connectors, 45 Degree Male, .63-.75", 3/4", Aluminum

## Application

45 Degree Male- Form 3

## Performance

- Environmental - Hazardous Locations - Used in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 in accordance with the NEC.
- Environmental - Operating Temperatures - -30°F to +225°F (-34°C to +107°C)

## General

Catalog Number	VHC1037
Color Code	Yellow
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Nylon Washer Between Box And Fitting.
Item Type	Cord Connectors
Material	Aluminum
Material - Mounting Hardware	Locknut or Tapped Opening
Series	Standard Duty
Specifications	<ul style="list-style-type: none"><li>• Cord Diameter Inches (mm) - .63"-.75"(15.9-19.0)</li><li>• Form Size - F3</li><li>• Material - Aluminum</li></ul>

Temperature Rating	• NPT Hub Size - 3/4 Inch Minimum -30 Deg F to 225 Deg F (-34 Deg C to 107 Deg C)
Type	45 Degree Male
UPC	783585202372

## Dimensions

Display Size	3/4" NPT
Hub Size	3/4"

## Conductor Related

Conductor Range	0.63- 0.75 in (15.9- 19.0 mm)
Number of Conductors	Single

## Certifications And Compliance

Industry Standard(s)	UL Listed
Nema Rating	NEMA Type 4, 4X, 12 and 13

## Logistics

Carton Quantity	15
-----------------	----

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Literature - Wire Management Solutions Brochure](#)  
[Specifications - VHC1037](#)  
[Warranty - Industrial & Commercial Products](#)