

Kellems Wire Management, Cord Connectors, 45 Degree Male, .75-.88", 1", Aluminum

By Hubbell Wiring Device-Kellems
Catalog # [VHC1042](#)



Kellems Wire Management, Cord Connectors, 45 Degree Male, .75-.88", 1", Aluminum

Application

45 Degree Male- Form 4

Performance

- Environmental - Hazardous Locations - Used in hazardous locations per Class I Div. 2, Class II Div. 1 & 2, Class III Div. 1 & 2 in accordance with the NEC.
- Environmental - Operating Temperatures - -30°F to +225°F (-34°C to +107°C)

General

Catalog Number	VHC1042
Color	Metallic
Color Code	Orchid
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Nylon Washer Between Box And Fitting.
Item Type	Cord Connectors
Material	Machined Aluminum
Material - Mounting Hardware Series	Locknut or Tapped Opening Standard Duty
Specifications	<ul style="list-style-type: none">• Cord Diameter Inches (mm) - .75"- .88"(19.0-22.2)• Form Size - F4• Material - Aluminum

Temperature Rating	<ul style="list-style-type: none">• NPT Hub Size - 1 Inch Minimum -30 Deg F to 225 Deg F (-34 Deg C to 107 Deg C)
Type	45° Male
UPC	783585202426

Dimensions

Display Size	1" NPT
Hub Size	1"

Conductor Related

Conductor Range	0.75- 0.88 in (19.0- 22.2 mm)
Number of Conductors	Single

Certifications And Compliance

Industry Standard(s)	UL Listed
Nema Rating	NEMA Type 4, 4X, 12 and 13

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Literature - Wire Management Solutions Brochure](#)
[Specifications - VHC1042](#)
[Warranty - Industrial & Commercial Products](#)