

## Wallplates and Boxes, Weatherproof Covers, 1-Gang, For Large Flanged Devices, Standard Size, Reinforced thermoplastic polyester

By Hubbell Wiring Device-Kellems  
Catalog # [WP2](#)



Wallplates and Boxes, Weatherproof Covers, 1-Gang, For Large Flanged Devices, Standard Size, Reinforced thermoplastic polyester

### General

Catalog Number	WP2
Color	Gray
Construction	Molded
EU RoHS Indicator	Yes
Item Type	Weatherproofing Covers
Knockouts	None
Material	Polyester, Thermoplastic Reinforced (RTP)
Material - Mounting Hardware	Vertical FS/FD Mount-Mounting Screws
Number Of Outlets	1-Device
Number of Gang(s)	1-Gang
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Specifications	<ul style="list-style-type: none"><li>• Gasket - Neoprene</li><li>• Hinge Pin - Stainless steel</li><li>• Material - RTP</li><li>• Spring - Stainless steel</li></ul>
Style	For Flanged Inlets & Flanged Receptacles
Type	Covers
UPC	783585392288

### Dimensions

Dimensions	4.56 in x 1.29 in x 2.84 in
Display Size	1-Gang
Height	2.84 in
Length	4.56 in
Weight	0.3 lb
Width	1.29 in

### Certifications And Compliance

Industry Standard(s)	UL Listed
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	1
Pallet Quantity	1440

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Specifications - WP2](#)  
[Warranty - Industrial & Commercial Products](#)