



NEMA 4 JIC Continuous Hinge Quarter Turn 14X12X6 Carbon Steel - Gray

By Wiegmann
Catalog # [BN4141206CHQT](#)

NEMA 4 JIC Continuous Hinge Quarter Turn 14X12X6 Carbon Steel - Gray



*Representative Image

Features

- New 1/4 turn style JIC enclosure makes for easy door seal
- Eliminates the need for exterior clips to secure door shut
- 1/4 turn latch is interchangeable with many locking designs available to better suit the customer
- FTC flange around the entire door opening to channel liquids away
- ANSI 61 gray powder coat finish

General

Application	Ultimate Mini-Max™ Series enclosures are designed to house and protect electrical and electronic components from harsh, dirty environments. For use in installations where dirt, dust, oil, water and other contaminants are present. Streamlined styling, 1/4 turn latch and attractive durable finish compliment any high tech electronic equipment.
Color	Gray
Cover Type	Hinged Cover
Finish Type	Polyester Powder
Latches Type	1/4 Turn
Material	Carbon Steel
Mounting Type	External Mounting Plates
Number of Doors (Fixed)	1
Type	Enclosure
UPC	786725880249

Dimensions

Depth	6 in
Height	14 in
Weight	18 lb
Width	12 in

Certifications And Compliance

Certified Listed	cULus
Nema Rating	4, 12
UL Listed	Yes

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [3D Models - BN4141206CHQT](#)
- [Brochures - Ultimate Mini-Max™ JIC Box 1/4 Turn Style](#)
- [Brochures - Modify Enclosures and Panels in 3-5 days](#)
- [Catalogs - Wiegmann NEMA 4 Enclosures](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - HWDBN4141206CHQT-S](#)
- [Engineering Drawing - MOD Center Drawings Instructions](#)
- [Engineering Drawing - BN4141206CHQT-MOD](#)
- [Sales Drawings - BN4141206CHQT-S](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WIEG-BN4141206CHQT-SPEC-EN | REV 6/2024