

NEMA 4 JIC Continuous Hinge Quarter Turn 14X12X8 304 Stainless Steel

By Wiegmann
Catalog # [BN4141208CHQTSS](#)

NEMA 4 JIC Continuous Hinge Quarter Turn 14X12X8 304
Stainless Steel.

Features

- New 1/4 turn style JIC enclosure makes for easy door seal
- Eliminates the need for exterior clips to secure door shut
- 1/4 turn latch is interchangeable with many locking designs available to better suit the customer
- FTC flange around the entire door opening to channel liquids away
- Available in light grained finish 304 or 316 stainless steel

Application

Ultimate Mini-Max™ Series enclosures are designed to house and protect electrical and electronic components from harsh, dirty environments. For use in installations where dirt, dust, oil, water and other contaminants are present. Streamlined styling, 1/4 turn latch and attractive durable finish compliment any high tech electronic equipment.

General

Catalog Number	BN4141208CHQTSS
Cover Type	Hinged Cover
Knockouts	No
Latches Type	1/4 Turn
Material	Stainless Steel
Mounting Type	External Mounting Plates
Number of Doors (Fixed)	1
Series	BN4-CHQTSS
Type	Enclosure
UPC	786725883318



*Representative Image

Dimensions

Depth	8 in
Height	14 in
Weight	19 lb
Width	12 in

Certifications And Compliance

Certified Listed	cULus
Nema Rating	4, 4X, 12
UL Listed	Yes

Logistics

Carton Quantity	1
-----------------	---

Product Assets

[3D Models - BN4141208CHQTSS](#)
[Brochures - Ultimate Mini-Max™ JIC Box 1/4 Turn Style](#)
[Brochures - Modify Enclosures and Panels in 3-5 days](#)
[Catalogs - Section E Stainless Steel & Aluminium](#)
[Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
[Engineering Drawing - BN4141208CHQTSS-MOD](#)
[Engineering Drawing - MOD Center Drawings Instructions](#)
[Engineering Drawing - HWDBN4141208CHQTSS-S](#)
[Sales Drawings - HWDBN4141208CHQTSS-S](#)
[SDS - HCC SDS](#)
[Specifications - BN4141208CHQTSS](#)
[Terms and Conditions - HCC Terms & Conditions](#)