



# NEMA 4 JIC Continuous Hinge Quarter Turn 16X14X8 Carbon Steel - Gray

By Wiegmann  
Catalog # [BN4161408CHQT](#)

NEMA 4 JIC Continuous Hinge Quarter Turn 16X14X8 Carbon Steel - Gray



\*Representative Image

## Features

- New 1/4 turn style JIC enclosure makes for easy door seal
- Eliminates the need for exterior clips to secure door shut
- 1/4 turn latch is interchangeable with many locking designs available to better suit the customer
- FTC flange around the entire door opening to channel liquids away
- ANSI 61 gray powder coat finish

## General

Application	Ultimate Mini-Max™ Series enclosures are designed to house and protect electrical and electronic components from harsh, dirty environments. For use in installations where dirt, dust, oil, water and other contaminants are present. Streamlined styling, 1/4 turn latch and attractive durable finish compliment any high tech electronic equipment.
Color	Gray
Cover Type	Hinged Cover
Finish Type	Polyester Powder
Latches Type	1/4 Turn
Material	Carbon Steel
Mounting Type	External Mounting Plates
Number of Doors (Fixed)	1
Type	Enclosure
UPC	786725880294

## Dimensions

Depth	8 in
Height	16 in
Weight	20 lb
Width	14 in

## Certifications And Compliance

Certified Listed	cULus
Nema Rating	4, 12
UL Listed	Yes

## Logistics

Carton Quantity	1
-----------------	---

## Product Assets

- [3D Models - BN4161408CHQT](#)
- [Brochures - Ultimate Mini-Max™ JIC Box 1/4 Turn Style](#)
- [Brochures - Modify Enclosures and Panels in 3-5 days](#)
- [Catalogs - Wiegmann NEMA 4 Enclosures](#)
- [Customer Notices - Prop 65 - Cancer & Reproductive Harm Notice](#)
- [Engineering Drawing - MOD Center Drawings Instructions](#)
- [Engineering Drawing - HWDBN4161408CHQT-S](#)
- [Engineering Drawing - BN4161408CHQT-MOD](#)
- [Sales Drawings - BN4161408CHQT-S](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WIEG-BN4161408CHQT-SPEC-EN | REV 6/2024