



Filter Box Fan 230 Volt 630 Cubic Feet Per Minute 11.1X11.1

By Wiegmann
Catalog # [FBF1010230V](#)

Filter Box Fan 230 Volt 630 Cubic Feet Per Minute 11.1X11.1



*Representative Image

Features

- Fan and grille are constructed of high grade steel
- Available in 115V or 230V
- High airflow and low noise operation
- Grille and filter can be removed and washed as needed

General

Application	Cooling
Color	Silver
EU RoHS Indicator	No
Material	Steel
Type	Filter Box Fan
UPC	786725885770

Dimensions

Actual Depth	4.8 in
Actual Height	11.6 in
Actual Width	11.8 in
Depth	5 in
Height	12 in
Width	12 in

Electrical Ratings

Wattage	63 W
---------	------

Certifications And Compliance

Certified Listed	UL/cUL Recognized
------------------	-------------------

Logistics

Carton Quantity	4
-----------------	---

Product Assets

[Brochures - Environmental Controls - Thermal Products](#)

[Catalogs - Wiegmann Environmental Controls](#)

[Engineering Drawing - FBF1010](#)

[Sales Drawings - FBF1010-43778h](#)

[SDS - HCC SDS](#)

[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand