



# Filter Box Fan 230 Volt 117 Cubic Feet Per Minute 5.6X5.6

By Wiegmann  
Catalog # [FBF44230V](#)

Filter Box Fan 230 Volt 117 Cubic Feet Per Minute 5.6X5.6



\*Representative Image

## Features

- Fan and grille are constructed of high grade steel
- Available in 115V or 230V
- High airflow and low noise operation
- Grille and filter can be removed and washed as needed

## Application

Cooling

## General

Color	Silver
EU RoHS Indicator	No
Material	Steel
Type	Filter Box Fan
UPC	786725885732

## Dimensions

Actual Depth	2.6 in
Actual Height	6.2 in
Actual Width	6.3 in
Depth	3 in
Height	6 in
Width	6 in

## Electrical Ratings

Wattage 21 W

## Certifications and Compliance

Certified Listed UL/cUL Recognized

## Logistics

Carton Quantity 10

## Product Assets

[Brochures - Environmental Controls - Thermal Products](#)  
[Catalogs - Wiegmann Environmental Controls](#)  
[Engineering Drawing - FBF44](#)  
[Sales Drawings - FBF44-43776h](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
WIEG-FBF44230V-SPEC-EN | REV 1/2024