



Filter Box Fan 115 Volt 239 Cubic Feet Per Minute 7.2X7.2

By Wiegmann

Catalog # [FBF66115V](#)

Filter Box Fan 115 Volt 239 Cubic Feet Per Minute 7.2X7.2



*Representative Image

Features

- Fan and grille are constructed of high grade steel
- Available in 115V or 230V
- High airflow and low noise operation
- Grille and filter can be removed and washed as needed

General

Application	Cooling
Color	Silver
Material	Steel
Type	Filter Box Fan
UPC	786725885749

Dimensions

Actual Depth	3.2 in
Actual Height	7.6 in
Actual Width	7.9 in
Depth	3 in
Height	8 in
Width	8 in

Electrical Ratings

Wattage	27 W
---------	------

Certifications And Compliance

Certified Listed	UL/cUL Recognized
------------------	-------------------

Logistics

Carton Quantity	6
-----------------	---

Product Assets

[Brochures - Environmental Controls - Thermal Products](#)

[Catalogs - Wiegmann Environmental Controls](#)

[Engineering Drawing - FBF66](#)

[Sales Drawings - FBF66-43777h](#)

[SDS - HCC SDS](#)

[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand