



Filter Box Fan 230 Volt 239 Cubic Feet Per Minute 7.2X7.2

By Wiegmann
Catalog # [FBF66230V](#)

Filter Box Fan 230 Volt 239 Cubic Feet Per Minute 7.2X7.2



*Representative Image

Features

- Fan and grille are constructed of high grade steel
- Available in 115V or 230V
- High airflow and low noise operation
- Grille and filter can be removed and washed as needed

Application

Cooling

General

Color	Silver
EU RoHS Indicator	No
Material	Steel
Type	Filter Box Fan
UPC	786725885756

Dimensions

Actual Depth	3.2 in
Actual Height	7.6 in
Actual Width	7.9 in
Depth	3 in
Height	8 in
Width	8 in

Electrical Ratings

Wattage 26 W

Certifications and Compliance

Certified Listed UL/cUL Recognized

Logistics

Carton Quantity 6

Product Assets

[Brochures - Environmental Controls - Thermal Products](#)
[Catalogs - Wiegmann Environmental Controls](#)
[Engineering Drawing - FBF66](#)
[Sales Drawings - FBF66-43777h](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WIEG-FBF66230V-SPEC-EN | REV 1/2024