

**NEMA 12 Filter Fan 24 Volt DC 132  
Cubic Feet Per Minute 9.8X9.8 -  
Black**

By Wiegmann  
Catalog # [FF1010132CFM24VB](#)



NEMA 12 Filter Fan 24 Volt DC 132 Cubic Feet Per Minute 9.8X9.8  
- Black

**Features**

- Available in gray or black
- Polyurethane foam gasketed seal on the mounting frame
- Shielded and self lubricating ball bearing fans
- Low noise operation

**Application**

- Ventilation
- Temperature Control

**General**

Catalog Number	FF1010132CFM24VB
Color	Black
Cutout	8.81x8.81
EU RoHS Indicator	No
Material	ABS Plastic
Type	Filter Fan
UPC	786725886760

**Dimensions**

Actual Depth	4.9 in
--------------	--------

Actual Height	9.8 in
Actual Width	9.8 in
Depth	5 in
Height	10 in
Width	10 in

**Electrical Ratings**

Voltage Rating	24 VDC
----------------	--------

**Certifications And Compliance**

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	UL/cUL Recognized

**Logistics**

Carton Quantity	10
-----------------	----

**Product Assets**

[Brochures - Environmental Controls - Thermal Products](#)  
[Catalogs - Section M Environmental Controls](#)  
[SDS - HCC SDS](#)  
[Specifications - FF1010132CFM24VB](#)  
[Terms and Conditions - HCC Terms & Conditions](#)