



NEMA 12 Filter Fan 48 Volt DC 132 Cubic Feet Per Minute 9.8X9.8 - Black

By Wiegmann
Catalog # [FF1010132CFM48VB](#)



NEMA 12 Filter Fan 48 Volt DC 132 Cubic Feet Per Minute 9.8X9.8 - Black

Features

- Available in gray or black
- Polyurethane foam gasketed seal on the mounting frame
- Shielded and self lubricating ball bearing fans
- Low noise operation

Application

- Ventilation
- Temperature Control

General

Color	Black
Cutout	8.81x8.81
EU RoHS Indicator	No
Material	ABS Plastic
Type	Filter Fan
UPC	786725886784

Dimensions

Actual Depth	4.9 in
Actual Height	9.8 in
Actual Width	9.8 in
Depth	5 in
Height	10 in
Width	10 in

Electrical Ratings

Voltage Rating	48 VDC
----------------	--------

Certifications and Compliance

Certified Listed	UL/cUL Recognized
------------------	-------------------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Brochures - Environmental Controls - Thermal Products](#)
[Catalogs - Wiegmann Environmental Controls](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WIEG-FF1010132CFM48VB-SPEC-EN | REV 1/2024