



# NEMA 12 Filter Fan 230 Volt 71 Cubic Feet Per Minute 9.8X9.8 - Black

By Wiegmann  
Catalog # [FF101071CFM230VB](#)



NEMA 12 Filter Fan 230 Volt 71 Cubic Feet Per Minute 9.8X9.8 -Black

## Features

- Available in gray or black
- Polyurethane foam gasketed seal on the mounting frame
- Shielded and self lubricating ball bearing fans
- Low noise operation

## Application

- Ventilation
- Temperature Control

## General

Color	Black
Cutout	8.81x8.81
EU RoHS Indicator	No
Material	ABS Plastic
Type	Filter Fan
UPC	786725886708

## Dimensions

Actual Depth	4.9 in
Actual Height	9.8 in
Actual Width	9.8 in
Depth	5 in
Height	10 in
Width	10 in

## Electrical Ratings

Voltage Rating	230 VAC
----------------	---------

## Certifications and Compliance

Certified Listed	UL/cUL Recognized
------------------	-------------------

## Logistics

Carton Quantity	10
-----------------	----

## Product Assets

[Brochures - Environmental Controls - Thermal Products](#)  
[Catalogs - Wiegmann Environmental Controls](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
WIEG-FF101071CFM230VB-SPEC-EN | REV 1/2024