



# NEMA 12 Filter Fan 230 Volt 340 Cubic Feet Per Minute 12.8X12.8 Light Gray

By Wiegmann  
Catalog # [FF1313340CFM230VG](#)



NEMA 12 Filter Fan 230 Volt 340 Cubic Feet Per Minute 12.8X12.8  
Light Gray

### Features

- Available in gray or black
- Polyurethane foam gasketed seal on the mounting frame
- Shielded and self lubricating ball bearing fans
- Low noise operation

### Application

- Ventilation
- Temperature Control

### General

Catalog Number	FF1313340CFM230VG
Color	Gray
EU RoHS Indicator	No
Material	ABS Plastic
Type	Filter Fan
UPC	786725886876

### Dimensions

Actual Depth	6.3 in
Actual Height	12.8 in
Actual Width	12.8 in
Depth	6 in
Height	13 in
Width	13 in

### Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	UL/cUL Recognized

### Logistics

Carton Quantity	4
-----------------	---

### Product Assets

- [Brochures - Environmental Controls - Thermal Products](#)
- [Catalogs - Section M Environmental Controls](#)
- [SDS - HCC SDS](#)
- [Specifications - FF1313340CFM230VG](#)
- [Terms and Conditions - HCC Terms & Conditions](#)