



NEMA 12 Filter Fan 115 Volt 547 Cubic Feet Per Minute 12.8X12.8 Light Gray

By Wiegmann
Catalog # [FF1313547CFM115VG](#)



NEMA 12 Filter Fan 115 Volt 547 Cubic Feet Per Minute
12.8X12.8 Light Gray

Features

- Available in gray or black
- Polyurethane foam gasketed seal on the mounting frame
- Shielded and self lubricating ball bearing fans
- Low noise operation

Application

- Ventilation
- Temperature Control

General

Color	Gray
EU RoHS Indicator	No
Material	ABS Plastic
Type	Filter Fan
UPC	786725886913

Dimensions

Actual Depth	6.3 in
Actual Height	12.8 in
Actual Width	12.8 in
Depth	6 in
Height	13 in
Width	13 in

Certifications and Compliance

Certified Listed	UL/cUL Recognized
------------------	-------------------

Logistics

Carton Quantity	12
-----------------	----

Product Assets

[Brochures - Environmental Controls - Thermal Products](#)
[Catalogs - Wiegmann Environmental Controls](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WIEG-FF1313547CFM115VG-SPEC-EN | REV 1/2024