



NEMA 12 Filter Fan 230 Volt 547 Cubic Feet Per Minute 12.8X12.8 - Black

By Wiegmann
Catalog # [FF1313547CFM230VB](#)



NEMA 12 Filter Fan 230 Volt 547 Cubic Feet Per Minute 12.8X12.8 -Black

Features

- Available in gray or black
- Polyurethane foam gasketed seal on the mounting frame
- Shielded and self lubricating ball bearing fans
- Low noise operation

Application

- Ventilation
- Temperature Control

General

Catalog Number	FF1313547CFM230VB
Color	Black
Cutout	11.49x11.49
EU RoHS Indicator	No
Material	ABS Plastic
Type	Filter Fan
UPC	786725886944

Dimensions

Actual Depth	6.3 in
--------------	--------

Actual Height	12.8 in
Actual Width	12.8 in
Depth	6 in
Height	13 in
Width	13 in

Electrical Ratings

Voltage Rating	230 VAC
----------------	---------

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	UL/cUL Recognized

Logistics

Carton Quantity	12
-----------------	----

Product Assets

[Brochures - Environmental Controls - Thermal Products](#)
[Catalogs - Section M Environmental Controls](#)
[SDS - HCC SDS](#)
[Specifications - FF1313547CFM230VB](#)
[Terms and Conditions - HCC Terms & Conditions](#)