



# NEMA 12 Filter Fan 230 Volt 9 Cubic Feet Per Minute 4.2X4.2 - Black

By Wiegmann  
Catalog # [FF449CFM230VB](#)

NEMA 12 Filter Fan 230 Volt 9 Cubic Feet Per Minute 4.2X4.2 - Black



\*Representative Image

## Features

- Available in gray or black
- Polyurethane foam gasketed seal on the mounting frame
- Shielded and self lubricating ball bearing fans
- Low noise operation

## Application

- Ventilation
- Temperature Control

## General

Color	Black
Cutout	3.63x3.63
EU RoHS Indicator	No
Material	ABS Plastic
Type	Filter Fan
UPC	786725886388

## Dimensions

Actual Depth	2.6 in
Actual Height	4.2 in
Actual Width	4.2 in
Depth	3 in
Height	4 in
Width	4 in

## Electrical Ratings

Voltage Rating	230 VAC
----------------	---------

## Certifications and Compliance

Certified Listed	UL/cUL Recognized
------------------	-------------------

## Logistics

Carton Quantity	16
-----------------	----

## Product Assets

[Brochures - Environmental Controls - Thermal Products](#)  
[Catalogs - Wiegmann Environmental Controls](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
WIEG-FF449CFM230VB-SPEC-EN | REV 1/2024