



NEMA 12 Filter Fan 24 Volt DC 9 Cubic Feet Per Minute 4.2X4.2 - Light Gray

By Wiegmann
Catalog # [FF449CFM24VG](#)



*Representative Image

NEMA 12 Filter Fan 24 Volt DC 9 Cubic Feet Per Minute 4.2X4.2 - Light Gray

Features

- Available in gray or black
- Polyurethane foam gasketed seal on the mounting frame
- Shielded and self lubricating ball bearing fans
- Low noise operation

Application

- Ventilation
- Temperature Control

General

Catalog Number	FF449CFM24VG
Color	Gray
EU RoHS Indicator	No
Material	ABS Plastic
Type	Filter Fan
UPC	786725886333

Dimensions

Actual Depth	2.1 in
Actual Height	4.2 in
Actual Width	4.2 in
Depth	2 in
Height	4 in
Width	4 in

Certifications And Compliance

Certified Listed	UL/cUL Recognized
------------------	-------------------

Logistics

Carton Quantity	16
-----------------	----

Product Assets

- [Brochures - Environmental Controls - Thermal Products](#)
- [Catalogs - Wiegmann Environmental Controls](#)
- [SDS - HCC SDS](#)
- [Specifications - FF449CFM24VG](#)
- [Terms and Conditions - HCC Terms & Conditions](#)