



NEMA 12 Filter Fan 48 Volt DC 28 Cubic Feet Per Minute 5.9X5.9 - Light Gray

By Wiegmann
Catalog # [FF6628CFM48VG](#)

NEMA 12 Filter Fan 48 Volt DC 28 Cubic Feet Per Minute 5.9X5.9 - Light Gray



*Representative Image

Features

- Available in gray or black
- Polyurethane foam gasketed seal on the mounting frame
- Shielded and self lubricating ball bearing fans
- Low noise operation

Application

- Ventilation
- Temperature Control

General

Catalog Number	FF6628CFM48VG
Color	Gray
EU RoHS Indicator	No
Material	ABS Plastic
Type	Filter Fan
UPC	786725886470

Dimensions

Actual Depth	2.9 in
Actual Height	5.9 in
Actual Width	5.9 in
Depth	3 in
Height	6 in
Width	6 in

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	UL/cUL Recognized

Logistics

Carton Quantity	20
-----------------	----

Product Assets

- [Brochures - Environmental Controls - Thermal Products](#)
- [Catalogs - Section M Environmental Controls](#)
- [SDS - HCC SDS](#)
- [Specifications - FF6628CFM48VG](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand