



# NEMA 12 Filter Fan 230 Volt 28 Cubic Feet Per Minute 5.9X5.9 - Black

By Wiegmann  
Catalog # [FF6629CFM230VB](#)

NEMA 12 Filter Fan 230 Volt 28 Cubic Feet Per Minute 5.9X5.9 -Black



\*Representative Image

## Features

- Available in gray or black
- Polyurethane foam gasketed seal on the mounting frame
- Shielded and self lubricating ball bearing fans
- Low noise operation

## Application

- Ventilation
- Temperature Control

## General

Color	Black
Cutout	4.95x4.95
EU RoHS Indicator	No
Material	ABS Plastic
Type	Filter Fan
UPC	786725886524

## Dimensions

Actual Depth	2.9 in
Actual Height	5.9 in
Actual Width	5.9 in
Depth	3 in
Height	6 in
Width	6 in

## Electrical Ratings

Voltage Rating	230 VAC
----------------	---------

## Certifications and Compliance

Certified Listed	UL/cUL Recognized
------------------	-------------------

## Logistics

Carton Quantity	20
-----------------	----

## Product Assets

[Brochures - Environmental Controls - Thermal Products](#)  
[Catalogs - Wiegmann Environmental Controls](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
WIEG-FF6629CFM230VB-SPEC-EN | REV 1/2024