



# NEMA 12 Filter Fan 115 Volt 65 Cubic Feet Per Minute 8X8 -Black

By Wiegmann  
Catalog # [FF8865CFM115VB](#)

NEMA 12 Filter Fan 115 Volt 65 Cubic Feet Per Minute 8X8 - Black



## Features

- Available in gray or black
- Polyurethane foam gasketed seal on the mounting frame
- Shielded and self lubricating ball bearing fans
- Low noise operation

## Application

- Ventilation
- Temperature Control

## General

Color	Black
Cutout	7x7
EU RoHS Indicator	No
Material	ABS Plastic
Type	Filter Fan
UPC	786725886609

## Dimensions

Actual Depth	3.8 in
Depth	4 in
Height	8 in
Width	8 in

## Electrical Ratings

Voltage Rating	115 VAC
----------------	---------

## Certifications and Compliance

Certified Listed	UL/cUL Recognized
------------------	-------------------

## Logistics

Carton Quantity	20
-----------------	----

## Product Assets

[Brochures - Environmental Controls - Thermal Products](#)  
[Catalogs - Wiegmann Environmental Controls](#)  
[Engineering Drawing - FF8865CFM\\_115\\_230V](#)  
[SDS - HCC\\_SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.  
WIEG-FF8865CFM115VB-SPEC-EN | REV 1/2024