



NEMA 12 Filter Fan 230 Volt 77 Cubic Feet Per Minute 8X8 -Black

By Wiegmann
Catalog # [FF8877CFM230VB](#)

NEMA 12 Filter Fan 230 Volt 77 Cubic Feet Per Minute 8X8 - Black



Features

- Available in gray or black
- Polyurethane foam gasketed seal on the mounting frame
- Shielded and self lubricating ball bearing fans
- Low noise operation

General

Application	Ventilation Temperature Control
Color	Black
Cutout	7x7
EU RoHS Indicator	No
Material	ABS Plastic
Type	Filter Fan
UPC	786725886661

Dimensions

Actual Depth	3.8 in
Depth	4 in
Height	8 in
Width	8 in

Electrical Ratings

Voltage Rating	230 VAC
----------------	---------

Certifications And Compliance

Certified Listed	UL/cUL Recognized
------------------	-------------------

Logistics

Carton Quantity	20
-----------------	----

Product Assets

- [Brochures - Environmental Controls - Thermal Products](#)
- [Catalogs - Wiegmann Environmental Controls](#)
- [SDS - HCC SDS](#)
- [Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand