



NEMA 12 Filter Fan 230 Volt 77 Cubic Feet Per Minute 8X8 -Light Gray

By Wiegmann
Catalog # [FF8877CFM230VG](#)



NEMA 12 Filter Fan 230 Volt 77 Cubic Feet Per Minute 8X8 - Light Gray

Features

- Available in gray or black
- Polyurethane foam gasketed seal on the mounting frame
- Shielded and self lubricating ball bearing fans
- Low noise operation

Application

- Ventilation
- Temperature Control

General

Color	Gray
EU RoHS Indicator	No
Material	ABS Plastic
Type	Filter Fan
UPC	786725886654

Dimensions

Actual Depth	3.8 in
Depth	4 in
Height	8 in
Width	8 in

Certifications and Compliance

Certified Listed	UL/cUL Recognized
------------------	-------------------

Logistics

Carton Quantity	20
-----------------	----

Product Assets

[Brochures - Environmental Controls - Thermal Products](#)
[Catalogs - Wiegmann Environmental Controls](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WIEG-FF8877CFM230VG-SPEC-EN | REV 1/2024