



Fan Heater 115/230 Volt 10 Cubic Feet Per Minute 350 Watts

By Wiegmann
Catalog # [FH115230V350W](#)

Fan Heater 115/230 Volt 10 Cubic Feet Per Minute 350 Watts



*Representative Image

Features

- Available in 115V or 230V
- Supplied with DIN rail clip installed
- Connection is a 3 screw terminal for 14 AWG

Application

Heating

General

Color	Black
EU RoHS Indicator	No
Material	Plastic
Type	Fan Heater
UPC	786725886142

Dimensions

Actual Depth	3.1 in
Actual Height	3.6 in
Actual Width	2.1 in
Depth	3 in
Height	4 in
Width	2 in

Electrical Ratings

Wattage 350 W

Certifications and Compliance

Certified Listed UL/cUL Recognized

Logistics

Carton Quantity 10

Product Assets

[Brochures - Environmental Controls - Thermal Products](#)
[Catalogs - Wiegmann Environmental Controls](#)
[Engineering Drawing - FH115230V_300_350W](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WIEG-FH115230V350W-SPEC-EN | REV 1/2024