



Fan Heater 115 Volt 16 Cubic Feet Per Minute 200 Watts

By Wiegmann
Catalog # [FH115V200W](#)

Fan Heater 115 Volt 16 Cubic Feet Per Minute 200 Watts



*Representative Image

Features

- Built in adjustable thermostat
- Auto fan control switch
- Integrated overheat protection

General

Application	Heating
Catalog Number	FH115V200W
Color	Silver
EU RoHS Indicator	No
Material	Stainless Steel
Type	Fan Heater
UPC	786725885985

Dimensions

Actual Depth	4.5 in
Actual Height	5.4 in
Actual Width	4.1 in
Depth	5 in
Height	6 in
Width	4 in

Electrical Ratings

Voltage Rating	115 V
Wattage	200 W

Certifications And Compliance

Certified Listed	UL/cUL Recognized
------------------	-------------------

Logistics

Carton Quantity	60
-----------------	----

Product Assets

[Brochures - Environmental Controls - Thermal Products](#)
[Catalogs - Wiegmann Environmental Controls](#)
[Engineering Drawing - FH115V125W-FH230V200W](#)
[SDS - HCC SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand