



Fan Heater 115 Volt 20 Cubic Feet Per Minute 250 Watts

By Wiegmann
Catalog # [FH115V250W](#)

Fan Heater 115 Volt 20 Cubic Feet Per Minute 250 Watts



*Representative Image

Features

- Available in 115V or 230V
- Supplied with DIN rail clip installed
- Connection is a 3 screw terminal for 14 AWG

Application

Heating

General

Color	Gray
Material	Plastic
Type	Fan Heater
UPC	786725886050

Dimensions

Actual Depth	3.2 in
Actual Height	5.3 in
Actual Width	4.4 in
Depth	3 in
Height	5 in
Width	4 in

Electrical Ratings

Voltage Rating	115 V
Wattage	250 W

Certifications and Compliance

Certified Listed	UL/cUL Recognized
------------------	-------------------

Logistics

Carton Quantity	1
-----------------	---

Product Assets

[Brochures - Environmental Controls - Thermal Products](#)
[Catalogs - Wiegmann Environmental Controls](#)
[Engineering Drawing - FHseries](#)
[SDS - HCC_SDS](#)
[Terms and Conditions - HCC Terms & Conditions](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WIEG-FH115V250W-SPEC-EN | REV 1/2024