



# Fan Heater 115 Volt 20 Cubic Feet Per Minute 500 Watts

By Wiegmann  
Catalog # [FH115V500W](#)

Fan Heater 115 Volt 20 Cubic Feet Per Minute 500 Watts



\*Representative Image

## Features

- Available in 115V or 230V
- Supplied with DIN rail clip installed
- Connection is a 3 screw terminal for 14 AWG

## General

|                   |              |
|-------------------|--------------|
| Application       | Heating      |
| Color             | Gray         |
| EU RoHS Indicator | No           |
| Material          | Plastic      |
| Type              | Fan Heater   |
| UPC               | 786725886098 |

## Dimensions

|               |        |
|---------------|--------|
| Actual Depth  | 3.2 in |
| Actual Height | 6.5 in |
| Actual Width  | 4.4 in |
| Depth         | 3 in   |
| Height        | 7 in   |
| Width         | 4 in   |

## Electrical Ratings

|                |       |
|----------------|-------|
| Voltage Rating | 115 V |
| Wattage        | 500 W |

## Certifications And Compliance

|                  |                   |
|------------------|-------------------|
| Certified Listed | UL/cUL Recognized |
|------------------|-------------------|

## Logistics

|                 |   |
|-----------------|---|
| Carton Quantity | 1 |
|-----------------|---|

## Product Assets

[Brochures - Environmental Controls - Thermal Products](#)  
[Catalogs - Wiegmann Environmental Controls](#)  
[Engineering Drawing - FHseries](#)  
[SDS - HCC SDS](#)  
[Terms and Conditions - HCC Terms & Conditions](#)



A Hubbell brand