



# Fan Heater 115 Volt 26 Cubic Feet Per Minute 750 Watts

By Wiegmann  
Catalog # [FH115V750W](#)

Fan Heater 115 Volt 26 Cubic Feet Per Minute 750 Watts



\*Representative Image

## Features

- Available in 115V or 230V
- Supplied with DIN rail clip installed
- Connection is a 3 screw terminal for 14 AWG

## Application

Heating

## General

Catalog Number	FH115V750W
Color	Gray
EU RoHS Indicator	No
Material	Plastic
Type	Fan Heater
UPC	786725886111

## Dimensions

Actual Depth	3.2 in
Actual Height	8.8 in
Actual Width	4.4 in
Depth	3 in

Height	9 in
Width	4 in

## Electrical Ratings

Voltage Rating	115 V
Wattage	750 W

## Certifications And Compliance

Buy American Compliant Certified Listed	Contact Manufacturer UL/cUL Recognized
---	--

## Logistics

Carton Quantity	1
-----------------	---

## Product Assets

[Brochures - Environmental Controls - Thermal Products](#)  
[Catalogs - Wiegmann Environmental Controls](#)  
[Engineering Drawing - FHseries](#)  
[SDS - HCC SDS](#)  
[Specifications - FH115V750W](#)  
[Terms and Conditions - HCC Terms & Conditions](#)