



Fan Heater 115 Volt 26 Cubic Feet Per Minute 750 Watts

By Wiegmann
Catalog # FH115V750W

Fan Heater 115 Volt 26 Cubic Feet Per Minute 750 Watts



*Representative Image

Features

- Available in 115V or 230V
- Supplied with DIN rail clip installed
- Connection is a 3 screw terminal for 14 AWG

Application

Heating

General

Catalog Number	FH115V750W
Color	Gray
EU RoHS Indicator	No
Material	Plastic
Type	Fan Heater
UPC	786725886111

Dimensions

Actual Depth	3.2 in
Actual Height	8.8 in
Actual Width	4.4 in

Depth	3 in
Height	9 in
Width	4 in

Electrical Ratings

Voltage Rating	115 V
Wattage	750 W

Certifications And Compliance

Certified Listed	UL/cUL Recognized
------------------	-------------------

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [Brochures - Environmental Controls - Thermal Products](#)
- [Catalogs - Wiegmann Environmental Controls](#)
- [Engineering Drawing - FHseries](#)
- [SDS - HCC SDS](#)
- [Specifications - FH115V750W](#)
- [Terms and Conditions - HCC Terms & Conditions](#)