

**Fan Heater 115 Volt 26 Cubic Feet
Per Minute 800 Watts**

By Wiegmann
Catalog # [FH115V800W](#)

Fan Heater 115 Volt 26 Cubic Feet Per Minute 800 Watts



*Representative Image

Features

- Built in adjustable thermostat
- Auto fan control switch
- Integrated overheat protection

Application

Heating

General

Catalog Number	FH115V800W
Color	Silver
EU RoHS Indicator	No
Material	Stainless Steel
Type	Fan Heater
UPC	786725886005

Dimensions

Actual Depth	4.5 in
Actual Height	7.5 in
Actual Width	4.1 in
Depth	5 in

Height	8 in
Width	4 in

Electrical Ratings

Voltage Rating	120 V
Wattage	800 W

Certifications And Compliance

Buy America(n) Qualified	Contact Manufacturer
Certified Listed	UL/cUL Recognized

Logistics

Carton Quantity	60
-----------------	----

Product Assets

[Brochures - Environmental Controls - Thermal Products](#)
[Catalogs - Section M Environmental Controls](#)
[Engineering Drawing - FH115V400W-FH230V800W](#)
[SDS - HCC SDS](#)
[Specifications - FH115V800W](#)
[Terms and Conditions - HCC Terms & Conditions](#)